

### TECHNICAL DATE SHEET

page 1/2

UVC multiple-lamp systems 400 W - **COMPACT T**

SYSTEM TYPE			3 AF400 T
Product			AQUAFIDES
Manufacturer			AQUAFIDES
DVGW type approval registry number - W294-2 (01.06.2006)			DW-9181BU0074
OPERATING RANGE			3 AF400 T
Flow rate certified (DVGW W294-2)	from - up to	m <sup>3</sup> /h	43,0 - 155,0
Interpolation between the test points allowed			yes
Head loss flow-max certified (without geodetical height)		bar	0,093
Fluenz - biososimetric (W294-2)		J/m <sup>2</sup>	400
Type approval according DVGW W294-2 (01.06.2006)			yes
Tr100 @ 254nm	from - up to	%	7 - 100
Tr50 @ 254nm	from - up to	%	26,5 - 100
Tr10 @ 254nm	from - up to	%	76,7 - 100
SSK @ 254nm	from - up to	m-1	11,6 - 0
Temperature of process water*	from - up to	°C	0 - 65
CONTROL - CABINET			3 AF400 T
Type			DigiSys with Slave Card 3 AF 300-400
System design			Bus-RS485
Control mode			digital
Control data and software update access			USB
Software service and settings via laptop			yes
Control display multi 3-colours (green, yellow and red)		lines	4
Control button for the operation of the system		button	5
Product (control-cabinet)			Rittal AE
Material (control-cabinet)			steel plate coated
Colour (control-cabinet)	grey	RAL	7035
Dimensions	width	mm	760
	height	mm	760
	depth	mm	300
Weight			kg
Operating voltage (nominal voltage)			V / Hz
Operating connection			0
Total consumed power (normal operation)			W
Power factor (normal operation)			cos φ
Current load per phase (by nominal voltage) max.			A
Protection class			IP
Feed line fuse (data for cutout type D)			pc x A
UVC lamp cable length (control-cabinet/reactor)			m
Power line cable length (control-cabinet/power plug)			m
Environmental temperature control-cabinet			°C
EVG ELECTRONIC BALLAST			3 AF400 T
Type			EVG 300 - 400 3,4 Ampere PH
Design		EVG	housing
Number of EVG's		pcs	3
UVC lamps per EVG		pcs	1
System design			Bus-RS485
Control mode			digital
UVC power line regulation			%
Overall efficiency (normal operation EVG and UVC lamp)			%

### TECHNICAL DATE SHEET

page 2/2

UVC multiple-lamp systems 400 W - **COMPACT T**

IRRADIATION CHAMBER			3 AF400 T
Irradiation chamber connection			0
Connecting dimensions acc. Norm (flange made of compressed plate)			DN 150
Design - lay-out inlet to outlet flange			DIN 2642
Irradiation chamber possible fitting positions			U - design
horizontal			yes
vertical			yes
reverse (UVC lamp)			yes
Material water-swept parts			stainless steel
Material number			1.4404
Material water-swept seals			O-rings
Dimensions			EPDM
width		mm	364
height (length)		mm	1.584
depth		mm	285
ED Ø		mm	256
Height IC including disassembling of the quartz tube			mm
Quartz tubes flanged with adapter			ED Ø
		mm	38
		length	mm
			1.607
Number of quartz tubes			pcs
			3
Weight without medium			approx. kg
			64
Weight with medium			approx. kg
			120
Irradiation chamber volume			approx. l
			56
Drain / vent			1/2"
Irradiation chamber protection class			IP
			65
Operating pressure (maximal)			bar
			10
UVC LAMP			3 AF400 T
Type			AF400A
Product / Manufacturer			AQUAFIDES
Number of UVC lamps			pcs
			3
UVC lamp kind			amalgam
UVC lamp power (Watt UVC per lamp - new lamp)			130,7
UVC lamp power (Watt UVC after 8.760 running hours per lamp) W (UVC)			91,5
UVC lamp power @ 253,7 nm			%
			≥ 85
UVC lamp wavelength @ ≤ 240 nm			filtrated
Power consumption per UVC lamp (including EVG)			W
			395
UVC lamp currentconsumption per UVC lamp (normal operation)			A
			3,4
UVC lamp connection			special
			4-pin
Lamp service life **			hours
			12.000
UVC SENSORSYSTEM			3 AF400 T
Type			DigiNorm
Numbers of UVC sensors			pc
			1
Design according ÖNORM M5873-1D			yes
Type tested according ÖNORM M5873-1D			yes
Recalibration according ÖNORM M5873-1D			yes
Calibration according ÖNORM M 5873-1D			yes
Recalibration time period			year
			1
System design UVC sensor			Bus-RS485
Control mode			digital
UV measurement range			W/m <sup>2</sup>
			2 - 500
Output signal (switchable)			mA
			0/4 - 20
Exactness of the measurements			%
			± 2
Sensitive @ 254 nm			%
			≥ 99
Temperature stability			°C
			0 - 75
UVC sensor cable length			m
			9

\* Medium temperature: in connection with the disinfection performance – please absolutely taking into account at dimensioning the plants

\*\* Lamp guarantee and usage agreements are mentioned in the general Terms and Conditions of UVC lamps